

DOOR & FRAME SCHEDULE																
MARK	ROOM NO.	ROOM NAME	OPERATION	DOOR				FRAME			RATING	HDWR	COMMENTS			
				WIDTH	HEIGHT	R.O. WID	R.O. HGT	TYPE	MATL	THICK				PANEL WIDTH	TYPE	MATL
LEVEL 1	100	CORRIDOR	Single - Hinged + Transom	3'-0"	7'-0"	4'-8"	8'-4"	V	WD	134"	3'-0"	6	HM	45 MIN		
102	102	TLT-P	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
103	103	TLT-P	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
105	152	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
107	107	TLT-P	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
108	108	PRE-OP	Single - Hinged + Transom	3'-0"	7'-0"	4'-8"	8'-4"	V	WD	134"	3'-0"	6	HM	45 MIN		
110	112	EXIT CORRIDOR	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	N	WD	134"	3'-0"	1	HM	1 1/2 HR		
111	109	NURSE	Single - Pocket	3'-0"	7'-0"	3'-3"	7'-1 1/2"	N	WD	134"	3'-0"	1	HM	-		
112A.1	112	EXIT CORRIDOR	Single - Hinged + Sidelite	3'-0"	7'-0"	5'-0"	7'-2"	F	WD	134"	3'-0"	3	HM	-		
112A.2	112A	VESTIBULE	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	G	MTL	134"	3'-0"	EXIST	EXIST	-		
113	116	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
113S	124	CORR. ELEC.	Door Opening - No Panel	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
114	110	POST-OP	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
114A	114	TLT-P	Single - Hinged	1'-6"	7'-0"	1'-10"	7'-2"	F	WD	134"	1'-6"	1	HM	-		
115	142	EXIT CORRIDOR	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	1 1/2 HR		
115.1	115A	CL	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
116	116	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	N	WD	134"	3'-0"	1	HM	1 1/2 HR		
117.1	117	OR 2	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	G	WD	134"	3'-0"	1	HM	-		
117.2	117	OR 2	Single - Hinged	4'-0"	7'-0"	4'-4"	7'-2"	G	WD	134"	4'-0"	1	HM	-		
118.1	118	OR 1	Single - Hinged	4'-0"	7'-0"	4'-4"	7'-2"	G	WD	134"	4'-0"	1	HM	-		
118.2	132	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	G	WD	134"	3'-0"	1	HM	-		
119	108	PRE-OP	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
120	120	LASER EXAM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
121	121	QUIET CONSULT	Single - Hinged + Transom	3'-0"	7'-0"	4'-8"	8'-4"	FG	WD	134"	3'-0"	1	HM	-		
122A	122A	PUMP ROOM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
122B	108	PRE-OP	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	45 MIN.		
123	123	ANESTH. WORK	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	G	WD	134"	3'-0"	1	HM	-		
124	124	CORR. ELEC.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	0	HM	45 MIN.		FLUSH EDGE FRAME & CONCEALED HINGES
125A	125A	ELEV. MACHINE ROOM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		REUSE EXG-F-R. DOOR & FRAME REMOVED FROM ELEC. RM 125
126	108	PRE-OP	Double - Hinged	7'-0"	7'-0"	7'-4"	7'-2"	F	WD	134"	3'-6"	6	HM	-		
126.1	130	SEMI-RESTRICTED	Single - Hinged	4'-0"	7'-0"	4'-4"	7'-2"	G	WD	134"	4'-0"	1	HM	-		
126.2	132	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	G	WD	134"	3'-0"	1	HM	-		
127.1	130	SEMI-RESTRICTED	Single - Hinged	4'-0"	7'-0"	4'-4"	7'-2"	G	WD	134"	4'-0"	1	HM	-		
127.2	127	OR 4	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	G	WD	134"	3'-0"	1	HM	-		
128	128	CLEAN SUPPLY	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
129	129	INSTR. PROCESS	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
131	132	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	G	WD	134"	3'-0"	1	HM	-		
132A	132	STAFF CORR.	Double - Hinged	5'-0"	7'-0"	5'-4"	7'-2"	F	WD	134"	2'-6"	1	HM	45 MIN.		
135	135	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	45 MIN.		
135A	135A	VEST.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	45 MIN.		
136	135	STAFF CORR.	Double - Hinged	5'-0"	7'-0"	5'-4"	7'-2"	F	WD	134"	2'-6"	1	HM	-		
137	137	PGC MED GAS	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
138.1	135	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
138.2	135A	VEST.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	45 MIN.		
138A	138	W LOCKER	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
138B	138B	STAFF SHOWER	Single - Wall Slider	3'-0"	7'-0"	3'-4"	6'-8"	F	WD	134"	3'-0"	1	HM	-		
139.1	135	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
139.2	135A	VEST.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	45 MIN.		
139A	139	M LOCKER	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
140.1	140	SHARED CORR.	Single - Hinged	3'-6"	7'-0"	3'-10"	7'-2"	F	MTL	134"	3'-6"	2	HM	-		
140.2	106	ENTRY LOBBY	Single - Hinged	3'-6"	7'-0"	3'-10"	7'-2"	F	WD	134"	3'-6"	1	HM	45 MIN.		
141	141	SOILED PICKUP	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	45 MIN.		
142	142	MED. STOR.	Single - Hinged	3'-6"	7'-0"	3'-10"	7'-2"	F	WD	134"	3'-6"	1	HM	45 MIN.		
143	143	PGC STOR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	45 MIN.		
144	100	CORRIDOR	Double - Hinged + Transom	6'-0"	7'-0"	6'-4"	7'-2"	FG	WD	134"	3'-0"	6	HM	-		
145.1	145	VESTIBULE	Double - Hinged + Transom	6'-0"	7'-0"	6'-4"	7'-2"	S2	ALUM.	134"	3'-0"	2	ALUM.	-		
145.2	145	VESTIBULE	Double - Hinged + Transom	6'-0"	7'-0"	6'-4"	7'-2"	S2	ALUM.	134"	3'-0"	2	ALUM.	-		
146A	146A	TLT-S	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	EXIST	134"	3'-0"	-	EXIST	-		EXISTING DOOR TO REMAIN. NEW HARDWARE SET
146B	146B	TLT-S	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	EXIST	134"	3'-0"	-	EXIST	-		EXISTING DOOR TO REMAIN. NEW HARDWARE SET
147	147	STAFF BREAK CONF	Single - Hinged + Sidelite	3'-0"	7'-0"	5'-0"	7'-2"	F	WD	134"	3'-0"	3	HM	-		
147A	147A	STOR.	Double - Hinged	5'-0"	7'-0"	5'-4"	7'-2"	F	WD	134"	2'-6"	1	HM	-		
148	148	LASIK PROCEDURE	Single - Hinged	3'-0"	7'-0"	3'-10"	7'-2"	F	WD	134"	3'-6"	1	HM	-		
148A	148A	PROCED.	Single - Wall Slider	3'-0"	7'-0"	3'-4"	6'-8"	F	WD	134"	3'-0"	1	HM	-		
152	152	STAFF CORR.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
182	182	STAIR NO. 2	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	1 1/2 HR		
E112.1	112	EXIT CORRIDOR	Double - Unequal	5'-0"	7'-0"	5'-4"	7'-2"	F	EXIST	134"	3'-0"	-	EXIST	-		CLEAN & CONFIRM ALL ASSEMBLIES IN WORKING ORDER
E150	150	SPKR. CL.	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	EXIST	134"	3'-0"	-	EXIST	-		EXISTING DOOR & FRAME TO BE PAINTED TO MATCH ADJACENT WALLS
LEVEL 2	201	RECEPTION	Single - Pocket	3'-6"	7'-6"	3'-9"	7'-1 1/2"	G	WD	134"	3'-6"	-	-	-		
202	202	TLT-P	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
203	203	TLT-P	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
204	204	CHECK-OUT	Single - Hinged + Sidelite	3'-0"	7'-0"	5'-0"	7'-2"	F	WD	134"	3'-0"	3	HM	-		
205	270	CIRCULATION	Single - Hinged + Sidelite	3'-0"	7'-0"	5'-0"	7'-2"	V	WD	134"	3'-0"	3	HM	-		
206.1	260	RETINA EAST WAITING	Single - Hinged + Sidelite	3'-0"	7'-0"	4'-8"	8'-4"	V	WD	134"	3'-0"	3	HM	-		
206.2	206	RETINA WEST WAITING	Single - Hinged + Sidelite + Transom	3'-0"	7'-0"	4'-8"	8'-4"	V	WD	134"	3'-0"	3	HM	-		
206A	206A	QUIET	Single - Wall Slider	3'-6"	7'-0"	3'-4"	6'-8"	FG	WD	134"	3'-6"	-	-	-		
207	207	EXAM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
208	208	EXAM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
209	209	EXAM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
210	210	EXAM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
211	211	RESEARCH EXAM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
212	220	CIRCULATION	Single - Hinged + Sidelite	3'-0"	7'-0"	5'-0"	7'-2"	F	WD	134"	3'-0"	3	HM	-		
213	213	EXAM	Single - Hinged	3'-0"	7'-0"	3'-4"	7'-2"	F	WD	134"	3'-0"	1	HM	-		
214	214	EXAM	Single													