

PARTIAL SINGLE LINE DIAGRAM

ADDITIONAL EXISTING DEVICES FIRE ALARM POWER PANEL GROUND FLOOR (AREA OF PROPOSED WORK) FIRE ALARM CONTROL PANEL BASEMENT FLOOR

NOTES:

RISER DIAGRAM IS DIAGRAMMATIC REFER TO PLANS FOR QUANTITIES AND LOCATIONS. PROVIDE ALL NECESSARY COMPONENTS TO COMPLETE A FULLY OPERATIONAL SYSTEM INCLUDING DEVICES LOCATED ON MECHANICAL DRAWINGS. ALL CABLING SHALL BE IN CONDUIT OR MC CABLE PER MANUFACTURERS REQUIREMENTS.

(E) - INDICATES EXISTING DEVICE TO REMAIN

(N) - INDICATES NEW DEVICE TO BE PROVIDED (R) - INDICATES EXISTING TO BE RELOCATED/EXISTING RELOCATED

0.4 KVA

0.35 KVA

0.3 KVA

1.05 KVA

3 AMPS

3 AMPS

3 AMPS

3 AVG. AMPS.

VERIFY DEVICE CAPACITY OF EXISTING CIRCUITS PRIOR TO BID AND PROVIDE NEW CIRCUIT(S) AND EXPANSION MODULES AS NEEDED.

COORDINATE ALL CONNECTIONS TO EXISTING SYSTEM WITH OWNER PRIOR TO BEGINNING WORK TO

CR2-86-G-1


PHASE A LOAD =

PHASE B LOAD =

PHASE C LOAD =

TOTAL LOAD=

N.T.S. 2 PARTIAL FIRE ALARM SYSTEM RISER DIAGRAM



—#12 COPPER GROUND FROM BUILDING STEEL TO GROUNDING STUD

1. PROVIDE INSTALLATION IN CHAMBER ROOM IN ACCORDANCE WITH NFPA 99, CHAPTER 20, 2012. PROVIDE WATERPROOF CONDUIT FOR CIRCUITS FEEDING THE CHAMBERS.

\ HYPERBARIC HEADWALL DETAIL E-3 /

	L2GN (NEW) FEED THROUGH LUGS																		208Y/120V, 3 phase 100 Amp MCB 100% NEUTRAL FULL GROUND BUS 10 KAIC	
CKT	DESCRIPTION	RECP	AC	HEAT	MECH	LTG	KITC	*	СВ	PH.	СВ	*	RECP	AC	HEAT	MECH	LTG	KITC	DESCRIPTION	CK
1	LTS. RM. 046							x 2	20/1	Α	20/1		0.9						CONSULT OFFICE RCPTS (5)	2
3	RECPT. RM. G115, G118, DOOR OPERATOR G	118						x	20/1	В	20/1		0.9						TREATMENT 4 RCPTS (5)	4
5	MULTI-PURP.& UTIL. RCPTS (5)	0.9							20/1	С	20/1	х							Lights in compressor room across from this pa	a 6
7	WTG ROOM POWERED DOOR	0.5				•			20/1	Α	20/1		0.9						TREATMENT 3 RCPTS (5)	8
9	GFI RECPT. RM. G118, RECPT. RM. 132C							x :	20/1	В	20/1		0.9						TREATMENT 2 RCPTS (5)	10
11	TREATMENT 1 RCPTS (5)	0.9							20/1	С	20/1	х							RECPT. RM. G049	12
13	ADMIN. RCPTS (4)	0.72							20/1	Α	20/1	х							RECPT. RM. G120	14
15	ADMIN. RCPTS (4)	0.72							20/1	В	20/1		0.72						WTG. RM RCPTS (4)	16
17	GFI RECPT. RM. 050							x :	20/1	С	20/1	х							RECPT. RM. G120, G122	18
19	FREIGHT ELEVATOR PIT PUMP G133C							x :	20/1	Α	20/1	х							LTS. RM. G114 CLOSET	20
21	VAV CIRCUIT	0.2							20/1	В	20/1	х							RECPT. IRRIGATION SYS. G115, NEXT TO PAI	N 22
23	HBO RM. CONV. & QUAD RCPTS. (6)	1.08							20/1	С	20/1	х							Compressor rm. w all recpt. Across from pane	el 24
25	FEED TO L2GNA							x (	60/3	Α	20/1	х							Compressor rm. w all recpt.	26
								х		В	20/1		0.36						CHAMBER QUAD RCPTS (2)	28
								х		С	20/1		0.36						CHAMBER QUAD RCPTS (2)	30
31	CORRIDOR RECEPTACLES (X)	0.72							20/1	Α	20/1		0.36						CHAMBER QUAD RCPTS (2)	32
33	WTG ROOM POWERED DOOR	0.5							20/1	В	20/1		0.36						CHAMBER QUAD RCPTS (2)	34
35	WTG ROOM POWERED DOOR	0.5							20/1	С	20/1								SPARE	36
37	SPARE								20/1	Α	20/1								SPARE	38
39	SPARE								20/1	В	20/1								SPARE	40
41	SPARE								20/1	С	20/1								SPARE	42
*	X. Circuits referenced to this note  1. Breakers referenced to this note  2. Breakers referenced to this note  PHASE A LOAD =	te shall l te shall l 4.1	pe GFI nave loo KVA	ckout pro	ovisions AMPS	anel; no	ew circu	(CC	ONNE	CTE	D LC		S)	20/2 = 20/3 = 30/2 = 30/3 = 40/2 =	2#12, # 3#12, # 2#10, # 3#10, # 2#8, #1	12GND 12GND 10GND 10GND 0GND IN	IN 3/4"0 IN 3/4"0 IN 3/4"0 IN 3/4"0 IN 3/4"0		E SIZES: 60/2 = 2#6, #10GND IN 3/4"C 60/3 = 3#6, #10GND IN 3/4"C 70/2 = 2#4, #8GND IN 1"C 70/3 = 3#4, #8GND IN 1"C 80/2 = 2#3, #8GND IN 1"C	
	PHASE B LOAD = PHASE C LOAD = TOTAL LOAD=	4.66 3.74		31	AMPS AMPS AVG. A	MDS		•	ONNE ONNE				S)	50/2 =	3#8, #10 2#6, #10 3#6, #10	OGND IN	√3/4"C		80/3 = 3#3, #8GND IN 1-1/4"C 90/2 = 2#2, #8GND IN 1"C 90/3 = 3#2, #8GND IN 1-1/4"C	

CKT		DESCRIPTION	RECP	AC	HEAT	MECH	LTG	KITC	* CB	PH.	СВ	* RECP	AC	HEAT MECH	LTG	KITC	DESCRIPTION	СКТ
1 s	SPARE								20/1	Α	20/1	0.2					CHAMBER RECEPTACLE (1)	2
3 s	SPARE								20/1	В	20/1	0.2					CHAMBER RECEPTACLE (1)	4
5 s	SPARE								20/1	С	20/1	0.2					CHAMBER RECEPTACLE (1)	6
7 s	SPARE								20/1	Α	20/1	0.2					CHAMBER RECEPTACLE (1)	8
9 s	SPARE								20/1	В	20/1				0.15		HYPERBARIC CHAMBER LTG.	10
11 s	SPARE								20/1	С	20/1	0.1					NURSE CALL EQUIPMENT	12
13 s	SPARE								20/1	Α	20/1						SPARE	14
15 s	SPARE								20/1	В	20/1						SPARE	16
<b>17</b> s	SPARE								20/1	С	20/1						SPARE	18
19 s	SPARE								20/1	Α	20/1						SPARE	20
<b>21</b> s	SPARE								20/1	В	20/1						SPARE	22
<b>23</b> s	SPARE								20/1	С	20/1						SPARE	24
<b>25</b> s	SPARE								20/1	Α	20/1						SPARE	26
<b>27</b> s	SPARE								20/1	В	20/1						SPARE	28
<b>29</b> s	SPARE								20/1	С	20/1						SPARE	30
31 s	SPARE								20/1	Α	20/1						SPARE	32
33 s	SPARE								20/1	В	20/1						SPARE	34
<b>35</b> s	SPARE								20/1	С	20/1						SPARE	36
37 s	SPARE								20/1	Α	20/1						SPARE	38
<b>39</b> s	SPARE								20/1	В	20/1						SPARE	40
<b>41</b> s	SPARE								20/1	С	20/1						SPARE	42

(CONNECTED LOADS)

(CONNECTED LOADS)

(CONNECTED LOADS)

40/2 = 2#8, #10GND IN 3/4"C

40/3 = 3#8, #10GND IN 3/4"C

50/2 = 2#6, #10GND IN 3/4"C

50/3 = 3#6, #10GND IN 3/4"C

208Y/120V, 3 phase

80/2 = 2#3, #8GND IN 1"C

90/2 = 2#2, #8GND IN 1"C

80/3 = 3#3, #8GND IN 1-1/4"C

90/3 = 3#2, #8GND IN 1-1/4"C

	GEN.	ATS-CR#2
	(480V, 1000kVA)	(480V, 400A)
EXISTING (KVA)	436.00	33.25
EXISTING (KVA) @125%	545.00	41.57
NEW (KVA)	0.95	0.95
TOTAL (KVA)	545.95	42.52
TOTAL (A)	656.70	51.14

N.T.S.	5	LOAD	CALCULATIONS	
	E-3			

Restorix Health® Excellence in Wound Care ARCHITECT m N OSKIN Tarytown, NY 10591 DENNIS CONSULTING MEDICAL CENTER N CAMPUS CARE AND C MEDICINE BRIGHTON C,
WOUND CAI
HYPERBARIC KEY PLAN: GROUND FLOOR ISSUE DATES: JANUARY 26, 2015 — STATE APPROVALS MARCH 20, 2015 → BLDG. DEPT. REVIEW DRAWN BY: CHECKED BY: | JZ

AS NOTED SCALE: | PROJECT NO.: | | P14110 SHEET TITLE: ELECTRICAL DIAGRAMS, DETAILS, AND SCHEDULES DRAWING NO.: